



:: MOUNTING PLATE - PERFORATED

| ORDER NO | TYPE | DESCRIPTION | DIMENSIONS | THICKNESS | QTY |
|----------|-----------|-----------------------------|------------|----------------|----------|
| 704 754 | D14D 0 0 | Manufina Blata Barfanata I | (WxH)mm | 0.00000 | 0.1 |
| 724 751 | PMP 2.2 | Mounting Plate - Perforated | 200x200mm | 2.0mm | 01 |
| 724 752 | PMP 2.2.5 | Mounting Plate - Perforated | 200x250mm | 2.0mm | 01 |
| 724 753 | PMP 2.3 | Mounting Plate - Perforated | 200x300mm | 2.0mm | 01 |
| | | | | | |
| 724 754 | PMP 2.5.3 | Mounting Plate - Perforated | 250x300mm | 2.0mm | 01 |
| | | Manualina Blata Bartanata I | | | |
| 724 760 | PMP 3.3 | Mounting Plate - Perforated | 300x300mm | 2.0mm | 01 |
| 724 761 | PMP 3.4 | Mounting Plate - Perforated | 300x400mm | 2.0mm | 01 |
| 724 762 | PMP 3.5 | Mounting Plate - Perforated | 300x500mm | 2.0mm | 01 |
| | | | | | |
| 724 764 | PMP 4.2.5 | Mounting Plate - Perforated | 400x250mm | 2.0mm | 01 |
| 724 765 | PMP 4.3 | Mounting Plate - Perforated | 400x300mm | 2.0mm | 01 |
| 724 766 | PMP 4.4 | Mounting Plate - Perforated | 400x400mm | 2.0mm | 01 |
| 724 767 | PMP 4.5 | Mounting Plate - Perforated | 400x500mm | 2.0mm | 01 |
| 724 768 | PMP 4.6 | Mounting Plate - Perforated | 400x600mm | 2.0mm | 01 01 |
| 724 769 | PMP 4.8 | Mounting Plate - Perforated | 400x800mm | 2.0mm 2.0mm | 01 |
| 724 770 | PMP 4.10 | Mounting Plate - Perforated | 400x1000mm | 2.0mm | 01 |
| | | | | | |
| 724 776 | PMP 5.4 | Mounting Plate - Perforated | 500x400mm | 2.0mm | 01 |
| 724 777 | PMP 5.5 | Mounting Plate - Perforated | 500x500mm | 2.0mm | 01 |
| 724 778 | PMP 5.6 | Mounting Plate - Perforated | 500x600mm | 2.0mm | 01 |
| 724 779 | PMP 5.7 | Mounting Plate - Perforated | 500x700mm | 2.0mm | 01 |
| | | | | | |
| 724 782 | PMP 6.4 | Mounting Plate - Perforated | 600x400mm | 2.0mm | 01 |
| 724 783 | PMP 6.5 | Mounting Plate - Perforated | 600x500mm | 2.0mm | 01 |
| 724 784 | PMP 6.6 | Mounting Plate - Perforated | 600x600mm | 2.0mm | 01 |
| 724 785 | PMP 6.8 | Mounting Plate - Perforated | 600x800mm | 2.0mm | 01 |
| 724 786 | PMP 6.10 | Mounting Plate - Perforated | 600x1000mm | 2.0mm | 01 |
| 724 787 | PMP 6.12 | Mounting Plate - Perforated | 600x1200mm | 2.0mm | 01 |
| 724 788 | PMP 6.14 | Mounting Plate - Perforated | 600x1400mm | 2.0mm | 01 |
| 724 790 | PMP 6.16 | Mounting Plate - Perforated | 600x1600mm | 2.0mm | 01 |
| | | | | | |
| 724 793 | PMP 8.6 | Mounting Plate - Perforated | 800x600mm | 2.0mm | 01 |
| 724 794 | PMP 8.8 | Mounting Plate - Perforated | 800x800mm | 2.0mm | 01 |
| 724 795 | PMP 8.10 | Mounting Plate - Perforated | 800x1000mm | 2.0mm | 01 |
| 724 796 | PMP 8.12 | Mounting Plate - Perforated | 800x1200mm | 2.0mm | 01 |
| 724 797 | PMP 8.14 | Mounting Plate - Perforated | 800x1400mm | 2.0mm | 01 |
| | | | | | |
| 724 799 | PMP 8.16 | Mounting Plate - Perforated | 800x1600mm | 2.0mm | 01 |

Other sizes are available on request.